

GL100 External Battery Kit



NAME	PART	DESCRIPTION
PCU / Motion Sensor		PCU manages the power from the external battery. It has a built in motion sensor and external digital input capability
Pelican 1020 Waterproof Box		All the components except the AC-DC charger will be put into the Pelican 1020 Waterproof Box
Frame for GL100 and PCU		The rubber frame is used to mount and stabilize the PCU / Motion sensor and the GL100 within the Pelican Micro 1020 Case
AC-DC Charger for External Battery		AC-DC charger is used to charge the external battery. Please NOTE that the PCU must be removed from the external battery when charging
External Battery		High capacity battery, 17600 mAh
GL100 to PCU Cable		This cable is used to connect the GL100 to PCU
PCU Digital Input Cable		This cable is used to connect external toggle switch / digital input to PCU

